


Product data sheet

Specifications

SQUARE D



Load center interior, QO, 1 phase, 12 spaces, 12 circuits, 200A convertible main lugs, NEMA3R, gnd bar, UL

QO112L200GRBI

! Discontinued

! Discontinued on: Mar 15, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Load Center Interior
Marketing Trade Name	QO
Load Center Type	Convertible Mains (lugs)
Rated Current	200 A
Number Of Spaces	12
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	12
Maximum Number Of Tandem Breakers	0
Number Of Phases	1 phase
Voltage Rating	120/240 V AC

Complementary

Ground Bar	Grounding bar included (not installed)
Busbar Material	Tin plated copper: busbar
Product Certifications	UL Listed
Tightening Torque	28 N.m, AWG 4...250 kcmil

Environment

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

Ordering and shipping details

Category	US10DE500199
Discount Schedule	0DE5
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	10.00 lb(US) (4.536 kg)
------------------	-------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	