





Load center, QO, 1 phase, 12 spaces, 24 circuits, 200A convertible main lugs, PoN, NEMA1, gnd bar, UL

QO112L200PG



! Discontinued on: Jun 30, 2023

Product availability: Stock - Normally stocked in distribution facility

### Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Grounding bar

## Complementary

Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)
Rated Current	200 A
Number Of Spaces	12
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	24
Maximum Number Of Tandem Breakers	12
Number Of Phases	1 phase
Ground Bar	Grounding bar included (not installed)
Box Number	9
Height	29.86 in (758.44 mm)
Width	14.25 in (361.95 mm)
Depth	3.75 in (95.25 mm)

#### **Environment**

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

## Ordering and shipping details

Category	US1DE3A10003
Discount Schedule	DE3A
Gtin	785001503638

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.10 in (10.414 cm)
Package 1 Width	15.00 in (38.1 cm)
Package 1 Length	31.00 in (78.74 cm)
Package 1 Weight	15.57 lb(US) (7.062 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov