

# Product data sheet

## Characteristics

# QO115GFICP

Mini CB, QO, 15 A, 1P, 120 V, 10 kA, Plug in, GFI, CP

Product availability : Stock - Normally stocked in distribution facility



Price\* : 233.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	15 A
System Voltage	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate
Type of packing	Consumer packaging

### Complementary

Interrupt Rating	10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.12 in
Depth	2.91 in
Width	0.75 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	01301 - QO-GFI BRKRS 1 POLE
Discount Schedule	CPQ
GTIN	00047569522314
Nbr. of units in pkg.	3
Package weight(Lbs)	0.5999999999999998
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1340 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>