

# Product data sheet

## Characteristics

# QO115VHPCAFI

Mini CB, QO, 15 A, 1P, 120 V, 22 kA, Plug in, CFI

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 534.00 USD



### Main

Product	Arc fault detection circuit breaker
Range	QO
Line Rated Current	15 A
System Voltage	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	PoN combination ARC-fault
Electrical Connection	Pressure plate

### Complementary

Interrupt Rating	22 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.75 in
Depth	2.91 in
Width	0.75 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

### Ordering and shipping details

Category	06303 - QO SINGLE POLE ARC FAULT CIRCUIT BREAKER
Discount Schedule	DE2A

GTIN	00785901849872
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	Y
Country of origin	MX

**Contractual warranty**

Warranty period	18 months
-----------------	-----------