





Mini circuit breaker, QO, 20A, 1 pole, 120VAC, 10kA, plug in, 6mA grd fault A, pigtail, aux switch 1B

QO120GFI1201

- ! Discontinued on: Dec 8, 2020
- ! End-of-service on: Dec 31, 2020

# (!) Discontinued

#### Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	20 A	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Circuit Breaker Type	Ground fault protecting class A 6 mA	
Ratings	Not rated	
Electrical Connection	Pressure plate	
Options	Auxiliary switch 120 V AC 1B	

#### Complementary

Interrupt Rating	10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium
Tightening Torque	35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	4.13 in (105 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.70 lb(US) (0.318 kg)

#### **Environment**

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

## Ordering and shipping details

Category	00003-QO 1&2 POLE GFI CB 30A MAX
Discount Schedule	DE2A
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	11.20 oz (317.515 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	End of Life Information