

Product data sheet

Characteristics

QO120GFI35

Mini CB, QO, 20 A, 1P, 120 V, 10 kA, Plug in, GFI, 50Deg

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 279.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	20 A
System Voltage	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.12 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00003 - QO 1&2 POLE GFI CB 30A MAX
----------	------------------------------------

Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	0.52000000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------