# Product data sheet

Specifications

SQUARE D





Load center, QO, 1 phase, 20 spaces, 24 circuits, 125A convertible main lugs, PoN, NEMA1, gnd bar, UL

QO120L125PG

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 324.00 USD

#### Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Grounding bar

## Complementary

Complementary	
Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)
Rated Current	125 A
Number Of Spaces	20
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	24
Maximum Number Of Tandem Breakers	4
Number Of Phases	1 phase
Ground Bar	Grounding bar included (not installed)
Box Number	6
Height	17.91 in (455 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)
Net Weight	11.79 lb(US) (5.350 kg)

### Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

## Ordering and shipping details

Category	US1DE3A10003
Discount Schedule	DE3A
Gtin	785901609407

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	Yes		
Country Of Origin	MX		
Packing Units			

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	14.44 in (36.672 cm)
Package 1 Length	18.19 in (46.197 cm)
Package 1 Weight	11.15 lb(US) (5.058 kg)

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

## **Certifications & Standards**

REACh Declaration	
Compliant	
EU RoHS Declaration	
China RoHS declaration	
Pro-active China RoHS declaration (out of China RoHS legal scope)	
Product Environmental Profile	
No need of specific recycling operations	
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	