

# Product data sheet

## Characteristics

# QO120PL

Mini CB, QO, 20 A, 1P, 120/240 V, 10 kA, Plug in, PL

Product availability : Stock - Normally stocked in distribution facility



Price\* : 125.00 USD



### Main

Product	Circuit breaker
Range	QO
Line Rated Current	20 A
System Voltage	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Provided equipment	18 in lead
Wire Size	AWG 12...AWG 2 (aluminium) AWG 14...AWG 2 (copper)
Height	4.55 in
Depth	2.91 in
Width	0.75 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	09650 - POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A
GTIN	00785901095705
Nbr. of units in pkg.	1
Package weight(Lbs)	0.47000000000000003
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1424 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------