

Product data sheet

Specifications



Mini circuit breaker, QO, 20A, 1 pole, 120/240VAC, 10kA, plug in, Powerlink, 60in leads

QO120PL5393

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 131.00 USD

Main

| | |
|-----------------------|--------------------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Current Rating | 20 A |
| Voltage Rating | 120/240 V AC 240 V AC 120 V AC |
| Mounting Type | Plug-in |
| Number Of Poles | 1P |
| Circuit Breaker Type | Standard |
| Ratings | HACR rated |
| Electrical Connection | Box lugs |

Complementary

| | |
|------------------------|--|
| Interrupt Rating | 10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC |
| Number Of Panel Spaces | 1 |
| Provided Equipment | 60 in (1524.00 mm) lead |
| Wire Size | AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper |
| Tightening Torque | 35.40 lbf.in (4 N.m) |
| Height | 4.57 in (116 mm) |
| Width | 0.75 in (19 mm) |
| Depth | 2.91 in (74 mm) |
| Net Weight | 0.60 lb(US) (0.272 kg) |

Environment

| | |
|----------------|------------------|
| Certifications | UL Listed CSA |
| Ambient Rating | 104 °F (40 °C) |

Ordering and shipping details

| | |
|----------|--------------|
| Category | US1DE8A09650 |
|----------|--------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|--------------|
| Discount Schedule | DE8A |
| Gtin | 785901404729 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.80 in (9.652 cm) |
| Package 1 Width | 1.30 in (3.302 cm) |
| Package 1 Length | 5.40 in (13.716 cm) |
| Package 1 Weight | 0.60 lb(US) (0.272 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

 Halogen Free Product

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65 WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov