

Product data sheet

Characteristics

QO120VH

QO mini breaker, 20 A, 1 pole, 120/240 V, 22 kA, plug in

Product availability : Stock - Normally stocked in distribution facility



Price* : 63.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	20 A
System Voltage	120 V AC 120/240 V AC 240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	Switching Duty rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	22 kA at: 120/240 V AC 50/60 Hz 22 kA at: 240 V AC 50/60 Hz 22 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
Discount Schedule	DE2A
GTIN	00785901371786
Nbr. of units in pkg.	10
Package weight(Lbs)	0.28000000000000003
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------