

Product data sheet

Characteristics

QO125EPD1201

Mini CB, QO, 25 A, 1P, 120 V, 10 kA, Plug in, EPD, Aux Switch 1B

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 542.00 USD



QO125EPD1201 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	25 A
System Voltage	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Ground fault protecting class B 30 mA
Ratings	Not rated
Electrical Connection	Pressure plate
Options	Auxiliary switch, 120 V AC, 1B contact(s)

Complementary

Interrupt Rating	10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.12 in
Depth	2.91 in
Width	1.5 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00910 - QO-EPD,QOB-EPD BREAKERS
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	0.25
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------