





Load center, QO, 1 phase, 30 spaces, 40 circuits, 200A convertible main lugs, PoN, NEMA1, gnd bar, combo cover, UL

QO130L200PGC

Product availability: Stock - Normally stocked in distribution facility

Price\*: 725.00 USD

### Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Combination flush/surface cover

## Complementary

Tightening Torque	Main lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper Main lugs 250 lb.in, AWG 4300 kcmil, aluminium/copper
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)
Rated Current	200 A
Number Of Spaces	30
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	40
Maximum Number Of Tandem Breakers	10
Number Of Phases	1 phase
Wire Size	AWG 6250 kcmil aluminium/copper
Ground Bar	Grounding bar included (not installed)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	9
Height	29.84 in (758 mm)
Width	14.25 in (362 mm)
Depth	0.01 in (0.15 mm)
Net Weight	27.49 lb(US) (12.470 kg)

#### **Environment**

Enclosure Rating NEMA 1 indoor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

# Ordering and shipping details

Category	US1DE3A10003
Discount Schedule	DE3A
Gtin	785901976448
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.60 in (14.224 cm)
Package 1 Width	16.30 in (41.402 cm)
Package 1 Length	32.40 in (82.296 cm)
Package 1 Weight	27.36 lb(US) (12.41 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	18
Package 2 Height	38.50 in (97.79 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	533.00 lb(US) (241.765 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov