

QO130VH1042

Mini CB, QO, 30 A, 1P, 120/240 V, 22 kA, Plug in, Shunt Trip



Price* : 261.00 USD



QO130VH1042 has not been replaced. Please contact your customer care center for more information.

Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	30 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Pressure plate
Options	Shunt trip, 12/24 V AC/DC,

Complementary

Interrupt Rating	22 kA at: 120 V AC 22 kA at: 120/240 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	1.5 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------