

Product data sheet

Characteristics

QO140HID

Mini CB, QO, 40 A, 1P, 120/240 V, 10 kA, Plug in, HID

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 38.10 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	40 A
System Voltage	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	High intensity discharge
Ratings	Not rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 8...AWG 2 (copper or aluminium)
Height	3.12 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00080 - QO SPECIALTY CB,1&2 POLE
----------	----------------------------------

Discount Schedule	DE2A
GTIN	00785901543749
Nbr. of units in pkg.	1
Package weight(Lbs)	0.31
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------