

QO140M200PRB

QO LoadCenter, PoN, main breaker, 200 A, 1 PH,
40 SP, NEMA3R



Main

Product	Load Center
Marketing Trade Name	QO
Load center type	Main breaker
Line Rated Current	200 A
Number of spaces	40
Short Circuit Current Rating	22 kA
Maximum Number of Single Pole Circuits	40
Maximum Number of Tandem Breakers	20
Phase	1 phase

Complementary

Enclosure Rating	NEMA 1
Box number	7R
Height	33.78 in
Width	14.75 in
Depth	4.52 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications