

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 73.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	40 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	22 kA at: 120/240 V AC 50/60 Hz 22 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 8...AWG 2 (copper or aluminium)
Height	3.12 in
Depth	2.91 in
Width	0.75 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

### Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
----------	-----------------------------

Discount Schedule	DE2A
GTIN	00785901014256
Nbr. of units in pkg.	1
Package weight(Lbs)	0.32000000000000001
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------