

Product data sheet

Characteristics

QO142L225PGCVP

QO LoadCTR, MainLugs, 225A, 1PH-3W, 42SP, NEMA1, Incl.Gnd.Bar, PON, Comb. CV, VP

Product availability : Stock - Normally stocked in distribution facility



Price* : 1,239.00 USD



Main

Product	Load Center value pack
Marketing Trade Name	QO
Load center type	Main lugs
Line Rated Current	225 A
Number of spaces	42
Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	42
Maximum Number of Tandem Breakers	0
Phase	1 phase

Complementary

Wire Size	AWG 6...300 kcmil (aluminium/copper)
Enclosure Rating	NEMA 1 indoor
Cover type	Combination flush/surface cover
Grounding Bar	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	3-wire
Busbar Material	Tin plated copper busbar
Enclosure Material	Welded sheet steel
Cover Finish	Baked enamel grey
Box number	11
Provided equipment	Circuit breaker 3 1P 20 A 120 V AC downstream Circuit breaker 2 2P 30 A 120/240 V AC downstream Load center 1 42P 225 A 120/240 V AC
Product certifications	UL listed

Height	37.99 in (965 mm)
Width	14.25 in (362 mm)

Ordering and shipping details

Category	00184 - MISC. QO 1PH LOAD CENTERS
Discount Schedule	DE3A
GTIN	00785901986188
Nbr. of units in pkg.	1
Package weight(Lbs)	35.420000000000002
Returnability	Y
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov