

# Product data sheet

## Characteristics

# QO142M200PC

QO LoadCenter, Main Breaker, 200A, 1PH-3W, 42SP, NEMA 1, Comb.CV, PON

Product availability : Stock - Normally stocked in distribution facility



Price\* : 1,360.00 USD



### Main

Product	Load Center
Marketing Trade Name	QO
Load center type	Main breaker
Line Rated Current	200 A
Number of spaces	42
Short Circuit Current Rating	22 kA
Maximum Number of Single Pole Circuits	42
Maximum Number of Tandem Breakers	0
Phase	1 phase

### Complementary

Wire Size	AWG 4...250 kcmil (aluminium/copper)
Enclosure Rating	NEMA 1 indoor
Cover type	Combination flush/surface cover
Grounding Bar	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Busbar Material	Tin plated copper busbar
Enclosure Material	Welded sheet steel
Cover Finish	Baked enamel grey
Box number	11
Product certifications	UL listed
Height	37.99 in (965 mm)
Width	14.25 in (362 mm)

## Ordering and shipping details

Category	10001 - QO PON 1PH LC,12-60 CKT, MB N1
Discount Schedule	DE3A
GTIN	00785901986898
Nbr. of units in pkg.	1
Package weight(Lbs)	35.399999999999999
Returnability	Y
Country of origin	US

## Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>