





Load center, QO, 1 phase, 42 spaces, 42 circuits, 200A convertible main breaker, PoN, NEMA1, combo cover, monitored, UL

QO142M200PCMR



Discontinued on: Jan 23, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

| Marketing Trade Name | QO   |  |
|----------------------|--|--|
| Product Type         | Load Center  |  |
| Cover Type           | Combination flush/surface cover                                      |  |
| Provided Equipment   | Circuit-breaker 1) 2P 200 A 120/240 V AC main supply ready assembled |  |

### Complementary

| Tightening Torque                      | Cover 20 lb.in                        |  |
|--|---------------------------------------|--|
| Pon Convertible Mains (Lugs)           | PoN Convertible Mains (breaker)       |  |
| Rated Current                          | 200 A                                 |  |
| Number Of Spaces                       | 42                                    |  |
| Max Short Circuit Current Rating       | 22 kA                                 |  |
| Bus Rated Current                      | 225 A                                 |  |
| Maximum Number Of Single Pole Circuits | 42                                    |  |
| Maximum Number Of Tandem Breakers      | 0                                     |  |
| Number Of Phases                       | 1 phase                               |  |
| Voltage Rating                         | 120/240 V AC                          |  |
| Wire Size                              | AWG 4300 kcmil copper or aluminium    |  |
| Number Of Monitored Circuits           | 18 maximum<br>6 standard              |  |
| Mounting Mode                          | Flush-mounted<br>Surface mounted      |  |
| Electrical Connection                  | Feed-thru lugs                        |  |
| Wiring Configuration                   | 3-wire                                |  |
| Busbar Material                        | Tin plated aluminium: busbar          |  |
| Enclosure Material                     | Welded sheet steel                    |  |
| Surface Finish                         | Baked enamel White                    |  |
| Product Compatibility                  | Electric vehicle ready<br>Solar ready |  |
| Height                                 | 37.99 in (965 mm)                     |  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Width | 14.25 in (362 mm) |
|-------|-------------------|
| Depth | 3.74 in (95 mm)   |

### Environment

| Enclosure Rating                      | NEMA 1 indoor                   |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature For Operation | 23 °F (-5 °C)<br>104 °F (40 °C) |
| Product Certifications                | UL Listed                       |

## Ordering and shipping details

| Category          | US1DE3A10001 |  |
|-------------------|--------------|--|
| Discount Schedule | DE3A         |  |
| Gtin              | 785901520313 |  |
| Returnability     | No           |  |
| Country Of Origin | US           |  |

# **Packing Units**

| Unit Type Of Package 1       | PCE                  |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 1.50 in (3.81 cm)    |
| Package 1 Width              | 1.50 in (3.81 cm)    |
| Package 1 Length             | 3.00 in (7.62 cm)    |
| Package 1 Weight             | 16 00 oz (453 592 g) |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Eu Rohs Directive         | Compliant   |
|---------------------------|---|
|                           | EU RoHS Declaration   |
| China Rohs Regulation     | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.  |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | End of Life Information   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |