Product data sheet

Specifications



Load center, QO, 1 phase, 4 spaces, 8 circuits, 125A fixed main lugs, NEMA3R, gnd bar, UL

QO148L125GRB

Product availability: Stock - Normally stocked in distribution facility

Price*: 152.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure
Cover Type	Surface cover

Complementary

Complementary	
Tightening Torque	Main lugs 50 lb.in, AWG 6AWG 2/0, aluminium/copper
Pon Convertible Mains (Lugs)	Fixed Mains (lugs)
Rated Current	125 A
Number Of Spaces	4
Max Short Circuit Current Rating	10 kA
Maximum Number Of Single Pole Circuits	8
Maximum Number Of Tandem Breakers	4
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 12AWG 2/0 aluminium AWG 14AWG 2/0 copper
Ground Bar	Grounding bar included (not installed)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded galvannealed steel
Surface Finish	Baked enamel Gray
Box Number	15R
Height	14.80 in (376 mm)
Width	8.90 in (226 mm)

Environment

Enclosure Rating	NEMA 3R outdoor
Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Certifications

UL Listed

Ordering and shipping details

Category	US1DE3A00101
Discount Schedule	DE3A
Gtin	785901484394
Returnability	Yes
Country Of Origin	MX

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	10.20 in (25.9 cm)
Package 1 Length	16.30 in (41.4 cm)
Package 1 Weight	11.42 lb(US) (5.18 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov