

Product data sheet

Characteristics

QO150

QO mini breaker, 50 A, 1 pole, 120/240 V, 10 kA, plug in

Product availability : Stock - Normally stocked in distribution facility



Price* : 29.10 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	50 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 8...AWG 2 (copper or aluminium)
Height	3.12 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00104 - QO 35-70A 1P;70-125A 2P CB
Discount Schedule	DE2A
GTIN	00785901400226
Nbr. of units in pkg.	10
Package weight(Lbs)	0.28000000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------