

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 50A, 1 pole, 120/240VAC, 10kA, plug in, ring

QO1505238

Discontinued on: Sep 19, 2022

Discontinued

## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	50 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Ring tongue

## Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m)
Height	3.11 in (79 mm)
Depth	2.91 in (74 mm)
Net Weight	0.32 lb(US) (0.145 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00004-QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.10 in (7.874 cm)
Package 1 Width	0.70 in (1.778 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	5.12 oz (145.15 g)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability





**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<hr/>		
<b>Eu Rohs Directive</b>		Compliant
		<a href="#">EU RoHS Declaration</a>
<hr/>		
<b>China Rohs Regulation</b>		<a href="#">China RoHS declaration</a>
		Pro-active China RoHS declaration (out of China RoHS legal scope)