

Product data sheet

Characteristics

QO150HID

Mini CB, QO, 50 A, 1P, 120/240 V, 10 kA, Plug in, HID

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 38.10 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	50 A
System Voltage	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	High intensity discharge
Ratings	Switching Duty rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 8...AWG 2 (copper or aluminium)
Height	3.12 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00080 - QO SPECIALTY CB,1&2 POLE
----------	----------------------------------

Discount Schedule	DE2A
GTIN	00785901543763
Nbr. of units in pkg.	10
Package weight(Lbs)	0.32000000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------