

Product data sheet

Characteristics

QO160

QO mini breaker, 60 A, 1 pole, 120/240 V, 10 kA, plug in

Product availability : Stock - Normally stocked in distribution facility



Price* : 29.10 USD



Main

| | |
|-----------------------|-------------------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Line Rated Current | 60 A |
| System Voltage | 120 V AC 120/240 V AC 48 V DC |
| Mounting Type | Plug-in |
| Number of Poles | 1P |
| Circuit Breaker Type | Standard |
| Ratings | HACR rated |
| Electrical Connection | Box lugs |

Complementary

| | |
|------------------------|--|
| Interrupt Rating | 5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz |
| Number of Panel Spaces | 1 |
| Wire Size | AWG 8...AWG 2 (copper or aluminium) |
| Height | 3.12 in |
| Depth | 2.91 in |
| Width | 0.75 in |

Environment

| | |
|----------------|------------------|
| Certifications | CSA UL listed |
| Ambient Rating | 104 °F (40 °C) |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 00104 - QO 35-70A 1P;70-125A 2P CB |
| Discount Schedule | DE2A |
| GTIN | 00785901477464 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.31 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant Schneider Electric declaration of conformity |
| REACH | Reference contains SVHC above the threshold Go to CaP for more details |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|