

# Product data sheet

## Characteristics

# QO1601200

Mini CB, QO, 60 A, 1P, 120/240 V, 10 kA, Plug in, Aux Switch 1A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 161.00 USD



QO1601200 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

### Main

|                       |   |
|-----------------------|---|
| Product               | Miniature circuit-breaker                 |
| Range                 | QO  |
| Line Rated Current    | 60 A                                      |
| System Voltage        | 120 V AC<br>120/240 V AC<br>48 V DC       |
| Mounting Type         | Plug-in                                   |
| Number of Poles       | 1P  |
| Circuit Breaker Type  | Standard                                  |
| Ratings               | HACR rated                                |
| Electrical Connection | Box lugs                                  |
| Options               | Auxiliary switch, 120 V AC, 1A contact(s) |

### Complementary

|                        |  |
|------------------------|--|
| Interruption Rating    | 5 kA at: 48 V DC<br>10 kA at: 120/240 V AC 50/60 Hz<br>10 kA at: 120 V AC 50/60 Hz |
| Number of Panel Spaces | 2  |
| Wire Size              | AWG 8...AWG 2 (copper or aluminium)  |
| Height                 | 3.12 in  |
| Depth                  | 2.91 in  |
| Width                  | 1.5 in   |

### Environment

|                |                  |
|----------------|------------------|
| Certifications | CSA<br>UL listed |
| Ambient Rating | 104 °F (40 °C)   |

### Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 00004 - QO,QOT 10-30A 1P;10-60A 2P |
| Discount Schedule     | DE2A                               |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 0.01                               |
| Returnability         | N                                  |

### Offer Sustainability

|                        |  |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant<br>Will be compliant   |
| REACH                  | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|