





# Mini circuit breaker, QO, 70A, 1 pole, 120/240VAC, 10kA, plug in

QO170

Product availability: Stock - Normally stocked in distribution facility

Price\*: 67.00 USD

#### Main

| Product               | Miniature circuit-breaker |
|-----------------------|---------------------------|
| Range                 | QO                        |
| Current Rating        | 70 A                      |
| Voltage Rating        | 120/240 V AC<br>120 V AC  |
| Mounting Type         | Plug-in                   |
| Number Of Poles       | 1P                        |
| Circuit Breaker Type  | Standard                  |
| Ratings               | HACR rated                |
| Electrical Connection | Box lugs                  |

## Complementary

| Interrupt Rating       | 10 kA 120/240 V AC<br>10 kA 120 V AC |
|------------------------|--------------------------------------|
| Number Of Panel Spaces | 1                                    |
| Wire Size              | AWG 8AWG 2 copper or aluminium       |
| Tightening Torque      | 44.25 lbf.in (5 N.m)                 |
| Height                 | 3.11 in (79 mm)                      |
| Width                  | 0.75 in (19 mm)                      |
| Depth                  | 2.91 in (74 mm)                      |
| Net Weight             | 0.31 lb(US) (0.141 kg)               |

### **Environment**

| Certifications | UL Listed<br>CSA |
|----------------|------------------|
| Ambient Rating | 104 °F (40 °C)   |

# Ordering and shipping details

| Category          | US1DE2A00104 |
|-------------------|--------------|
| Discount Schedule | DE2A         |
| Gtin              | 785901477471 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

| Unit Type Of Package 1       | PCE                         |
|------------------------------|-----------------------------|
| Number Of Units In Package 1 | 1                           |
| Package 1 Height             | 1.00 in (2.54 cm)           |
| Package 1 Width              | 3.60 in (9.144 cm)          |
| Package 1 Length             | 3.60 in (9.144 cm)          |
| Package 1 Weight             | 0.31 lb(US) (0.141 kg)      |
| Unit Type Of Package 2       | PAL                         |
| Number Of Units In Package 2 | 4032                        |
| Package 2 Height             | 40.00 in (101.6 cm)         |
| Package 2 Width              | 40.00 in (101.6 cm)         |
| Package 2 Length             | 48.00 in (121.92 cm)        |
| Package 2 Weight             | 1263.14 lb(US) (572.948 kg) |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

# Well-being performance

| <b>Ø</b> | Toxic Heavy Metal Free     |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Mercury Free               |     |
| <b>②</b> | Rohs Exemption Information | Yes |
| <b>⊘</b> | Halogen Free Product       |     |

# **Certifications & Standards**

| Reach Regulation      | REACh Declaration  |
|-----------------------|--|
| Eu Rohs Directive     | Compliant with Exemptions  |
| China Rohs Regulation | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information. |
| Circularity Profile   | No need of specific recycling operations   |