

Product data sheet

Characteristics

QO1DM10050TRBR

QO LoadCenter, Gen Panel, 100/50A,
1PH-3W,4SP,NEMA3R, Ftry.Gnd.Bar, Inter.
Hand.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 1,148.00 USD



Main

Product	Load Center
Marketing Trade Name	QO
Load center type	Fixed mains (back-fed main breakers)
Line Rated Current	100 A
Number of spaces	4
Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	8
Maximum Number of Tandem Breakers	4
Phase	1 phase

Complementary

Wire Size	AWG 8...AWG 2 (copper)
Enclosure Rating	NEMA 3R outdoor
Cover type	Surface cover
Grounding Bar	Grounding bar (factory installed)
Electrical connection	Lugs
Wiring configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded galvanized steel
Cover Finish	Baked enamel grey
Box number	17R
Product certifications	UL listed
Height	12.64 in (321 mm)

Width	8.9 in (226 mm)
-------	-----------------

Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901468806
Nbr. of units in pkg.	1
Package weight(Lbs)	12.220000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------