

# Product data sheet

## Characteristics

# QO2100VH1021

Mini CB, QO, 100 A, 2P, 120/240 V, 22 kA, Plug in, Shunt Trip

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 504.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	100 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	Shunt trip, 120/208/240 V AC,

### Complementary

Interrupt Rating	22 kA at: 120/240 V AC 50/60 Hz 22 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 4...AWG 2/0 (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	2.25 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	N
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------