

Product data sheet

Characteristics

QO2125CP

QO mini breaker, 125 A, 2 pole, 120/240 V, 10 kA, plug in, CP

Product availability : Stock - Normally stocked in distribution facility



Price* : 428.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	125 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Type of packing	Consumer packaging

Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 4...AWG 2/0 (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	1.5 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	01343 - QO 2 POLE 70-125 AMP
Discount Schedule	CPQ
GTIN	00047569044007
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7299999999999998
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

QO2125CP is replaced by:



QO(B) Circuit Breakers QO2125

QO mini breaker, 125 A, 2 pole, 120/240 V, 10 kA, plug in

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017