

Product data sheet

Specifications



Mini circuit breaker, QO, 125A, 2 pole, 120/240VAC, 22kA, plug in, alarm switch

QO2125VH2100

⚠ Discontinued on: Dec 8, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	125 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	Alarm switch 120 V AC 1A

Complementary

Interrupt Rating	22 kA 120/240 V AC 22 kA 120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening Torque	49.56 lbf.in (5.6 N.m)
Height	3.50 in (89 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.00 lb(US) (0.454 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926-QO IND SPECIALTY CB
Discount Schedule	DE2A
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.00 oz (453.592 g)

Contractual warranty

Warranty	18 months
----------	-----------