

Product data sheet

Characteristics

QO2151200

Mini CB, QO, 15 A, 2P, 120/240 V, 10 kA, Plug in, Aux Switch 1A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 199.00 USD



QO2151200 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	15 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Options	Auxiliary switch, 120 V AC, 1A contact(s)

Complementary

Interruption Rating	5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	2.25 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	0.95000000000000007
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------