

Product data sheet

Characteristics

QO215H5237

Mini CB, QO, 15 A, 2P, 120/240 V, 10 kA, Plug in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 240.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	15 A
System Voltage	120 V AC 120/240 V AC 240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Ring tongue

Complementary

Interruption Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 (copper)
Height	3 in
Depth	2.91 in
Width	1.5 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
Discount Schedule	DE2A
GTIN	00785901126713
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	Y
Country of origin	MX