

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 15A, 2 pole, 120VAC, 10kA, plug in, switch neutral, 50 deg C

QO215SWN35

Discontinued on: Jul 30, 2020  
End-of-service on: Sep 22, 2020

Discontinued

## Main

|                       |                           |
|-----------------------|---------------------------|
| Product               | Miniature circuit-breaker |
| Range                 | QO                        |
| Current Rating        | 15 A                      |
| Voltage Rating        | 120 V AC                  |
| Mounting Type         | Plug-in                   |
| Number Of Poles       | 2P                        |
| Circuit Breaker Type  | Switch neutral            |
| Ratings               | Not rated                 |
| Electrical Connection | Pressure plate            |

## Complementary

|                        |                                    |
|------------------------|------------------------------------|
| Interrupt Rating       | 10 kA 120 V AC                     |
| Number Of Panel Spaces | 2                                  |
| Wire Size              | AWG 14...AWG 8 copper or aluminium |
| Tightening Torque      | 35.40 lbf.in (4 N.m)               |
| Height                 | 2.99 in (76 mm)                    |
| Width                  | 1.50 in (38 mm)                    |
| Depth                  | 2.91 in (74 mm)                    |
| Net Weight             | 0.28 lb(US) (0.127 kg)             |

## Environment

|                |                  |
|----------------|------------------|
| Certifications | UL Listed<br>CSA |
| Ambient Rating | 122 °F (50 °C)   |

## Ordering and shipping details

|                   |                                |
|-------------------|--------------------------------|
| Category          | 00080-QO SPECIALTY CB,1&2 POLE |
| Discount Schedule | DE2A                           |
| Gtin              | 00785901725930                 |
| Returnability     | No                             |
| Country Of Origin | MX                             |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type Of Package 1       | PCE                 |
| Number Of Units In Package 1 | 1                   |
| Package 1 Height             | 2.30 in (5.842 cm)  |
| Package 1 Width              | 3.50 in (8.89 cm)   |
| Package 1 Length             | 3.80 in (9.652 cm)  |
| Package 1 Weight             | 4.48 oz (127.006 g) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|                       |                            |                                        |
|-----------------------|----------------------------|----------------------------------------|
| ✓                     | Reach Free Of Svhc         |                                        |
| ✓                     | Toxic Heavy Metal Free     |                                        |
| ✓                     | Mercury Free               |                                        |
| ✓                     | Rohs Exemption Information | Yes                                    |
|                       |                            |                                        |
| Eu Rohs Directive     |                            | Compliant                              |
|                       |                            | <a href="#">EU RoHS Declaration</a>    |
|                       |                            |                                        |
| China Rohs Regulation |                            | <a href="#">China RoHS declaration</a> |