

# Product data sheet

## Characteristics

# QO220C

## Mini CB, QO, 20 A, 2P, 120/240 V, 10 kA, Plug in

Product availability : Stock - Normally stocked in distribution facility



Price\* : 67.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	20 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Type of packing	Clam packaging

### Complementary

Interrupt Rating	5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	1.5 in

### Environment

Certifications	UL listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	01342 - QO 2 POLE CARDED BRKRS.
Discount Schedule	CPQ
GTIN	00047569522178
Nbr. of units in pkg.	3
Package weight(Lbs)	0.5899999999999997
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations