

Product data sheet

Characteristics

QO225PL

Mini CB, QO, 25 A, 2P, 120/240 V, 10 kA, Plug in, PL

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 455.00 USD



Main

Product	Circuit breaker
Range	QO
Line Rated Current	25 A
System Voltage	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz
Number of Panel Spaces	2
Provided equipment	18 in lead
Wire Size	AWG 12...AWG 2 (aluminium) AWG 14...AWG 2 (copper)
Tightening torque	4.6 N.m
Height	4.55 in
Depth	2.91 in
Width	1.5 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	09650 - POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A
GTIN	00785901095743
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8599999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
---------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------