

# Product data sheet

## Characteristics

# QO28035

Mini CB, QO, 80 A, 2P, 120/240 V, 10 kA, Plug in, 50Deg

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 227.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	80 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 4...AWG 2/0 (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	1.5 in

### Environment

Certifications	UL listed CSA
Ambient Rating	122 °F (50 °C)

Ordering and shipping details

Category	00080 - QO SPECIALTY CB,1&2 POLE
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7199999999999997
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

Contractual warranty

Warranty period	18 months
-----------------	-----------