

# Product data sheet

## Characteristics

# QO360CP

QO mini breaker, 60 A, 3 pole, 120/240 V, 10 kA, plug in, CP

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 248.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	60 A
System Voltage	120 V AC 120/240 V AC 240 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Type of packing	Consumer packaging

### Complementary

Interrupt Rating	5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 8...AWG 2 (copper or aluminium)
Height	3.12 in
Depth	2.91 in
Width	2.25 in

### Environment

Certifications	CSA UL listed
----------------	------------------

Ambient Rating	104 °F (40 °C)
----------------	----------------

### Ordering and shipping details

Category	01330 - QO-THREE POLE BRKRS.
Discount Schedule	CPQ
GTIN	00047569071881
Nbr. of units in pkg.	3
Package weight(Lbs)	0.8300000000000007
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### QO360CP is replaced by:



#### QO(B) Circuit Breakers QO360

QO mini breaker, 60 A, 3 pole, 120/240 V, 10 kA, plug in

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017