



Mini switch, QO, 100A, 2 pole, 120/240VAC, 10kA, bolt on

QOB2000

! Discontinued on: Jan 11, 2023

! Discontinued

Main

Product	Switch
Range	QO
Current Rating	100 A
Voltage Rating	120/240 V AC
Mounting Type	Bolt-on
Number Of Poles	2P
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC
Number Of Panel Spaces	2
Wire Size	AWG 42/0 kcmil copper or aluminium
Tightening Torque	49.56 lbf.in (5.6 N.m)
Height	3.50 in (89 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.56 lb(US) (0.254 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS DE2	
Discount Schedule		
Gtin	00785901120629	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of	Package 1	PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1 1

Package 1 Weight 8.96 oz (254.012 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)