





Mini circuit breaker, QO, 15A, 2 pole, 120/240VAC, 10kA, bolt on

QOB215

Product availability: Stock - Normally stocked in distribution facility

Price*: 91.54 USD

Main

man i		
Product	Miniature circuit-breaker	
Range	QO	
Current Rating	15 A	
Voltage Rating	120/240 V AC 120 V AC	
Mounting Type	Bolt-on	
Number Of Poles	2P	
Circuit Breaker Type	Standard	
Ratings	HACR rated	
Electrical Connection	Pressure plate	

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.60 lb(US) (0.272 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
Gtin	785901416821
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	9.59 oz (272.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.60 in (9.144 cm)
Package 2 Width	3.30 in (8.382 cm)
Package 2 Length	7.90 in (20.066 cm)
Package 2 Weight	2.80 lb(US) (1.27 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	8.60 in (21.844 cm)
Package 3 Width	8.30 in (21.082 cm)
Package 3 Length	17.20 in (43.688 cm)
Package 3 Weight	28.55 lb(US) (12.95 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov