

# Product data sheet

## Characteristics

# QOB245H

## Mini CB, QO, 45 A, 2P, 120/240 V, 10 kA, Bolt on

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 240.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	45 A
System Voltage	120 V AC 120/240 V AC 240 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 8...AWG 2 (copper or aluminium)
Tightening torque	4.6 N.m
Height	3.12 in
Depth	2.91 in
Width	1.5 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901487807
Nbr. of units in pkg.	1
Package weight(Lbs)	0.75
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
------------------------	--

## Contractual warranty

Warranty period	18 months
-----------------	-----------