

Product data sheet

Specifications

SQUARE D

Green Premium™



Mini circuit breaker, QO, 60A, 2 pole, 120/240VAC, 10kA, bolt on, Powerlink

QOB260PL

⚠ Discontinued on: Nov 25, 2022

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	60 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC
Number Of Panel Spaces	2
Provided Equipment	18 in (457.20 mm) lead
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening Torque	44.25 lbf.in (5 N.m)
Height	4.57 in (116 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.88 lb(US) (0.399 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE8A00912
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	DE8A
Gtin	785901095668
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.25 in (8.263 cm)
Package 1 Width	1.49 in (3.79 cm)
Package 1 Length	4.57 in (11.615 cm)
Package 1 Weight	14.08 oz (399.161 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration