

# Product data sheet

## Characteristics

# QOB280

QO mini breaker, 80 A, 2 pole, 120/240 V, 10 kA, bolt on

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 240.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	80 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 4...AWG 2/0 (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	1.5 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901019701
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7199999999999997
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------