# Product data sheet

Specifications

#### SQUARE D





# Mini circuit breaker, QO, 35A, 3 pole, 120/240VAC, 10kA, bolt on

QOB335

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 316.44 USD

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	35 A
Voltage Rating	120/240 V AC 240 V AC
	120 V AC
Mounting Type	Bolt-on
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

#### Complementary

Interrupt Rating	10 kA 120/240 V AC
	10 kA 240 V AC
	10 kA 120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.020.04 in² (1025 mm²) (AWG 8AWG 2)
Height	3.11 in (79 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.82 lb(US) (0.372 kg)

# Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

# Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
Gtin	785901368335
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of	Origin
------------	--------

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.03 in (7.7 cm)
Package 1 Width	3.03 in (7.7 cm)
Package 1 Length	3.11 in (7.9 cm)
Package 1 Weight	13.30 oz (377 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	864
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.03 in (122.0 cm)
Package 2 Weight	709.12 lb(US) (321.650 kg)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations