





Mini circuit breaker, QO, 60A, 3 pole, 120/240VAC, 10kA, bolt on

QOB360

Product availability: Stock - Normally stocked in distribution facility

Price*: 316.44 USD

Main

| ******* | | |
|-----------------------|--------------------------------------|--|
| Product | Miniature circuit-breaker | |
| Range | QO | |
| Current Rating | 60 A | |
| Voltage Rating | 120/240 V AC 240 V AC 120 V AC | |
| Mounting Type | Bolt-on | |
| Number Of Poles | 3P | |
| Circuit Breaker Type | Standard | |
| Ratings | HACR rated | |
| Electrical Connection | Box lugs | |

Complementary

| Interrupt Rating | 10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC |
|------------------------|--|
| Number Of Panel Spaces | 3 |
| Wire Size | AWG 8AWG 2 copper or aluminium |
| Tightening Torque | 44.25 lbf.in (5 N.m) |
| Height | 3.11 in (79 mm) |
| Width | 2.24 in (57 mm) |
| Depth | 2.91 in (74 mm) |
| Net Weight | 0.85 lb(US) (0.386 kg) |

Environment

| Certifications | UL Listed CSA |
|----------------|------------------|
| Ambient Rating | 104 °F (40 °C) |

Ordering and shipping details

| Category | US10DE200015 |
|-------------------|--------------|
| Discount Schedule | 0DE2 |
| Gtin | 785901417187 |
| Returnability | Yes |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.30 in (8.382 cm) |
| Package 1 Width | 3.00 in (7.62 cm) |
| Package 1 Length | 3.50 in (8.89 cm) |
| Package 1 Weight | 13.62 oz (386.0 g) |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 3.40 in (8.636 cm) |
| Package 2 Width | 2.80 in (7.112 cm) |
| Package 2 Length | 6.80 in (17.272 cm) |
| Package 2 Weight | 2.59 lb(US) (1.175 kg) |
| Unit Type Of Package 3 | CAR |
| Number Of Units In Package 3 | 36 |
| Package 3 Height | 3.30 in (8.382 cm) |
| Package 3 Width | 14.20 in (36.068 cm) |
| Package 3 Length | 21.70 in (55.118 cm) |
| Package 3 Weight | 32.00 lb(US) (14.515 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

| ⊘ | Toxic Heavy Metal Free | |
|----------|----------------------------|-----|
| Ø | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |
| ⊘ | Halogen Free Product | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|-----------------------|--|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Circularity Profile | No need of specific recycling operations |