

# Product data sheet


Specifications

SQUARE D



## Mini circuit breaker, QO, 25A, 1 pole, 240/415VAC, 3kA, bolt on

QOBXD125

 **Discontinued on:** Aug 25, 2023

 **Discontinued**

### Main

|                       |                           |
|-----------------------|---------------------------|
| Product               | Miniature circuit-breaker |
| Range                 | QO                        |
| Current Rating        | 25 A                      |
| Voltage Rating        | 240/415 V AC              |
| Mounting Type         | Bolt-on                   |
| Number Of Poles       | 1P                        |
| Circuit Breaker Type  | Standard                  |
| Ratings               | Not rated                 |
| Electrical Connection | Pressure plate            |

### Complementary

|                        |   |
|------------------------|---|
| Interrupt Rating       | Icu 3 kA 240/415 V AC IEC 947-2   |
| Number Of Panel Spaces | 1   |
| Tightening Torque      | 44.25 lbf.in (5 N.m) 0.02...0.04 in <sup>2</sup> (10...25 mm <sup>2</sup> ) (AWG 8...AWG 2) |
| Height                 | 2.99 in (76 mm)   |
| Width                  | 0.75 in (19 mm)   |
| Depth                  | 2.91 in (74 mm)   |
| Net Weight             | 0.31 lb(US) (0.141 kg)  |

### Environment

|                |                |
|----------------|----------------|
| Certifications | IEC            |
| Ambient Rating | 104 °F (40 °C) |

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 00920-QO INTERNATIONAL SENA |
| Discount Schedule | DE2A                        |
| Returnability     | No                          |
| Country Of Origin | MX                          |

### Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                     |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1                   |
| Package 1 Height             | 0.90 in (2.286 cm)  |
| Package 1 Width              | 3.50 in (8.89 cm)   |
| Package 1 Length             | 3.50 in (8.89 cm)   |
| Package 1 Weight             | 4.96 oz (140.614 g) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation