Product data sheet

Specifications

SQUARE D





Mini circuit breaker, QOU, 20A, 1 pole, 120/240VAC, 10kA

QOU120

Product availability: Stock - Normally stocked in distribution facility

Price*: 40.20 USD

Main

Product Or Component Type	Miniature circuit-breaker
Range Of Product	QOU
Circuit Breaker Type	Standard
Circuit Breaker Application	HACR rated

Complementary

j	
Line Rated Current	20 A
Electrical Connection	Slotted box lugs, line side
	Slotted box lugs, load side
[Ue] Rated Operational Voltage	120/240 V AC
	120 V AC
	48 V DC
Mounting Mode	Unit mount
Awg Gauge	AWG 14AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	0.75 in (19.05 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

Environment

CSA IEC UL Listed

Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901418535
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	0.36 in (0.914 cm)
Package 1 Width	0.16 in (0.406 cm)
Package 1 Length	0.49 in (1.245 cm)
Package 1 Weight	4.97 oz (141 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations