Product data sheet

Specifications





Mini switch, QOU, non-automatic, 60A, 2 pole, 240 VAC, 10kA

QOU200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 93.96 USD

Main

Product Or Component Type	Switch
Range Of Product	QOU
Circuit Breaker Application	HACR rated

Complementary

60 A
Slotted box lugs, line side Slotted box lugs, load side
Unit mount
AWG 12AWG 2/0 aluminium/copper
4.05 in (102.87 mm)
1.5 in (38.10 mm)
2.95 in (74.93 mm)
45 lbf.in (5.08 N.m) (AWG 14AWG 2)

Environment

Product Certifications

UL Listed CSA

Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901371717
Returnability	No
Country Of Origin	US

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	4.90 in (12.446 cm)
Package 1 Weight	11.20 oz (317.515 g)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations