

Product data sheet

Characteristics

QOU210

QOU Miniature Circuit Breaker, 10A, 2P,
120/240V, 10kA

Product availability : Stock - Normally stocked in distribution facility



Price** : 87.00 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	QOU
Circuit breaker type	Standard

Complementary

Line Rated Current	10 A
Number of Poles	2P
Interrupt Rating	10 kA at: 120/240 V AC 5 kA at: 48 V DC 10 kA at: 120 V AC
Electrical connection	Slotted box lugs, line side Slotted box lugs, load side
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting mode	Unit mount
AWG gauge	AWG 14...AWG 2 (aluminium/copper)
Height	4.45 in
Depth	2.95 in
Width	1.5 in
Tightening torque	45 lbf.in AWG 14...AWG 2

Environment

Product certifications	UL listed IEC CSA
------------------------	-------------------------

Ordering and shipping details

Category	00900 - QOU BREAKERS & SWITCH
Discount Schedule	DE2
GTIN	00785901477457
Nbr. of units in pkg.	24
Package weight(Lbs)	0.7399999999999999
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------