

# Product data sheet

Specifications



## Mini circuit breaker, QOU, 30A, 3 pole, 240VAC, 10kA

QOU330

Product availability: Stock - Normally stocked in distribution facility

Price\*: 307.80 USD

### Main

Product Or Component Type	Miniature circuit-breaker
Range Of Product	QOU
Circuit Breaker Type	Standard
Circuit Breaker Application	HACR rated

### Complementary

Line Rated Current	30 A
Electrical Connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] Rated Operational Voltage	120/240 V AC 240 V AC 120 V AC 48 V DC
Mounting Mode	Unit mount
Awg Gauge	AWG 14...AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	2.25 in (57.15 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14...AWG 2)

### Environment

Product Certifications	CSA UL Listed IEC
------------------------	-------------------------

### Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901418924
Returnability	Yes
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	4.80 in (12.192 cm)
Package 1 Weight	17.60 oz (498.952 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	3.50 in (8.89 cm)
Package 2 Width	13.40 in (34.036 cm)
Package 2 Length	20.50 in (52.07 cm)
Package 2 Weight	22.85 lb(US) (10.365 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	960
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	1086.00 lb(US) (492.601 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Halogen Free Product	

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations