SQUARE D





Mini circuit breaker, QOU, 45A, 3 pole, 240 VAC, 10kA, four point quick connect terminals

QOUQ345

Discontinued on: Jan 11, 2023

(!) Discontinued

Main

Product Or Component Type	Miniature circuit-breaker	
Range Of Product	QOU	
Circuit Breaker Type	Standard	
Circuit Breaker Application	HACR rated	

Complementary

Line Rated Current	45 A	
Electrical Connection	Slotted box lugs, line side Slotted box lugs, load side	
[Ue] Rated Operational Voltage	120/240 V AC 240 V AC 120 V AC 48 V DC	
Mounting Mode	Unit mount	
Awg Gauge	AWG 14AWG 2 aluminium/copper	
Height	4.05 in (102.87 mm)	
Width	2.25 in (57.15 mm)	
Depth	2.95 in (74.93 mm)	
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)	

Environment

Product Certifications		
Product Certifications	UL Listed	
	IFC	
	120	
	CSA	
	IEC CSA	

Ordering and shipping details

Category	00900-QOU BREAKERS & SWITCH	
Discount Schedule	DE2	
Gtin	00785901127178	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE		

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	4.70 in (11.938 cm)
Package 1 Weight	17.76 oz (503.488 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	